

MTS / T-BERD 6000AV2

B13451

RELEASE NOTE

Ste-Core Package 13451 (November 2013)

- Boot V4.92 (04/November/2013)
- Linux Kernel V6.32 (04/November/2013)
- File System V4.54 (04/November/2013)
- Instrument Setup V12.00 (04/November/2013)
- Microscope V12.00 (04/November/2013)

Ste-Optical Package 13451 (November 2013)

- Fiber Optics V12.00 (04/November/2013)

CONTENTS

T-BERD/MTS 6000AV2 Base Unit.....	3
New Functionalities	3
Improvements	3
FO Functions	3
New functionalities	3
Improvements	3
OTDR	3
New functionalities	3
Improvements	3
PMD/CD/AP Module	3
New functionalities	3
HR-OSA	4
New functionalities	4
FiberComplete	4
Improvements	4
Script	4
Improvements	4

T-BERD/MTS 6000AV2 Base Unit

New Functionalities

- Ability to add customer watermark logo using a license key
- FiberTrace Viewer executable file is now available on unit disk
- New automatic check disk on extended memory
- Possible use of proxy settings for Stratasync synchronization
- Management of floating licences with Stratasync

Improvements

- Chinese keyboard improvement for non-touchscreen product
- Improved battery management: no longer orange LED when battery is full, correction of wrong "battery too hot" message
- On/Off key less sensitive: longer key press
- Improved talkset/datalink management

FO Functions

New functionalities

- When generating report, ability to use the customer logo of the system setup
- Ability to increment/decrement fiber number with user define value

Improvements

- Ability to format disk even when other platform application is running (browser, calculator...)
- 4 digit available for fiber number (except FiberComplete IL/ORL function with 3 digit)

OTDR

New functionalities

- Addition of FTTH-SLM license option

Improvements

- Fault locator OTDR display now available on SmartOTDR mode
- Improvement of receive cable management when there is no trace on display
- Improvement of slope measurements with lock marker function

PMD/CD/AP Module

New functionalities

- For AP function, addition of C-band selection within the wavelength range
- For CD/PMD function, addition of pass/fail thresholds for 100 Gb/s

HR-OSA

New functionalities

- SMSR (DFB) functions
- Ability to move horizontal cursors
- Addition of On/Off OSNR function for in-band OSNR measurements on polarization multiplexed signals
- Addition of variable resolution settings

FiberComplete

Improvements

- Improved fiber number transfer between units

Script

Improvements

- Fiber Characterization script not managing Fcomp/Fchar modules are reactivated
- Improved management of BBS (from FChar module)